



849 Level Control

2.849.0010

Zusatzrüstung zu den Sample Processors zur Überwachung des Füllstandes in Spül- oder Abfallkanistern via Remote. Der 849 Level Control verhindert das Trockenlaufen der Pumpen und /oder das Überlaufen der Kanister und ist geeignet für den Einsatz in wässrigen Lösungen, Lösemitteln und Suspensionen.

Lieferumfang 2.849.0010

Qt.	Order no.	Beschreibung
1 PCS	1.849.0020	849 Level Control metal-free (for canisters)

Additional equipment for Metrohm instruments. For monitoring the filling level of bottles for eluent, auxiliary or waste solutions via remote control. The 849 Level Control prevents pumps from running dry and/or canisters from overflowing and is suitable for use with aqueous solutions, solvents and suspensions.

The metal-free sensor works in solutions with very low conductivity. Therefore it may be used in ion chromatography.



1 PCS

6.1113.000

Sensor for 849 Level Control

Sensor for 849 Level Control



1 PCS

6.2151.060

Cable for Level Control and Eluent Production Module

Connecting cable for sensor and Level Control or Eluent Production Module.

