




IC Conductivity Detector

2.850.9010

Kompakter und intelligenter Hochleistungs-Leitfähigkeits-Detektor zu den intelligenten IC Geräten. Hervorragende Temperaturkonstanz, die gesamte Signalverarbeitung innerhalb des geschützten Detektorblocks und DSP – Digital Signal Processing – der letzten Generation garantieren höchste Präzision der Messung. Dank dem dynamischen Arbeitsbereich sind keine (auch nicht automatische) Bereichswechsel notwendig.

Lieferumfang 2.850.9010

Qt.	Order no.	Beschreibung
1 PCS	1.850.9010	IC Conductivity Detector

Compact and intelligent high performance conductivity detector for intelligent IC instruments. Outstanding temperature stability, the complete signal processing within the protected detector block and the latest generation of DSP – Digital Signal Processing – guarantee the highest precision of the measurement. No change of measuring ranges (not even automatic ones) is required, due to the dynamic working range.



1 PCS

6.2744.014

Pressure screw 2x

With UNF 10/32 connection. For the connection of PEEK capillaries

