



Metrosep A Supp 17 - 100/4.0

6.01032.410

Die Metrosep A-Supp-17-Säulen sind Anionentrennsäulen für den Einsatz bei Raumtemperatur mit sehr gutem Preis/Leistungsverhältnis. Die Metrosep A Supp 17 - 100/4.0 ermöglicht die Trennung der Standardanionen in kurzer Zeit. Durch die hohe Flexibilität in der Flussrate (bis 1.8 mL/min) lassen sich, abhängig vom Trennproblem, sehr kurze Analysenzeiten erreichen.

Lieferumfang 6.01032.410

Qt.	Order no.	Beschreibung
2 PCS	6.2744.060	Threaded stopper

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Optionales Zubehör

Order no.	Beschreibung	
6.01032.500	Metrosep A Supp 17 Guard/4.0	
	The Metrosep A Supp 17 Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. Thanks to the "On Column Guard System", the guard column is very easy to handle. The guard column screws easily onto the analytical column. No tools are required.	
6.01032.510	Metrosep A Supp 17 S-Guard/4.0	
	The Metrosep A Supp 17 S-Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	
6.01032.530	Metrosep A Supp 17 S-Guard - 50/4.0	
	The Metrosep A Supp 17 S-Guard 50/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	