



Impact printer CUSTOM DP40-S4N

2.140.0200

Normal paper printer, paper width 58 mm (40 columns), serial interface RS 232C (DB9). U = 100...240 V, 50/60 Hz.

Below, the accessories are grouped into Scope of delivery and Optional accessories.
Please keep this printout at hand for ordering replacement material.
These lists may be subject to change.

Scope of delivery 2.140.0200

Qt.	Order no.	Description
1 PCS	1.140.0200	Impact printer CUSTOM DP40-S4N
		Normal paper printer, paper width 58 mm (40 columns), serial interface RS 232C (DB9). U = 100...240 V, 50/60 Hz.



Optional accessories

Order no.	Description	
6.2125.130	RS-232 cable, 1.8 m, DB25 (socket) – DB9 (plug) Connecting Metrohm RS-232 interface (DB25) to a Custom DP40 printer or Mettler PG 5200 balance.	
6.2134.110	Cable RS-232 DB9 socket f – DB9 plug Connecting Metrohm RS-232 interface (DB9) to a Custom DP40 printer. For Titrinos or 756/831 KF Coulometer. RS-232 extension cable (1:1)	