

947 Professional UV/VIS Detector Vario SW


2.947.0010

As an intelligent, single-wavelength detector, the 947 Professional UV/VIS Detector Vario SW permits a secure and reliable quantification of substances active in the ultraviolet or visible range. One wavelength can be selected.

Below, the accessories are grouped into Scope of delivery and Optional accessories. Please keep this printout at hand for ordering replacement material. These lists may be subject to change.

Scope of delivery 2.947.0010

Qt.	Order no.	Description
1 PCS	1.947.0010	Professional UV/VIS Detector Vario SW



2 PCS

6.1831.100

PEEK capillary 0.25 mm i.d., 1 m



1 PCS

6.2151.020

Cable USB A - USB B 1.8 m

USB connecting cable



1 PCS

6.2744.070

Pressure screw short

Short version. With UNF 10/32 connection. 5 pieces. For the connection of PEEK capillaries



1 PCS





6.2839.130

Flow-through cell for 944

PEEK flow-through cell for 944 Professional UV/VIS Detector Vario



Optional accessories

Order no.	Description	
2.943.0110	943 Professional Reactor Vario	
	<p>The 943 Professional Reactor Vario is a heatable reactor, especially developed for pre- and post-column derivatization. It captivates by its robustness, the fast heating rate and the possibility of carrying out reactions at up to 150 °C.</p>	
2.943.0210	943 Professional Thermostat Vario	
	<p>The 943 Professional Thermostat Vario is a stand-alone column oven for up to two columns with a maximum length of 150 mm. It captivates by its fast heating rate and the possibility of operating two separation columns together at up to 80°C.</p>	
6.2061.100	Bottle holder for Professional IC instruments	
	<p>Instrument cover and bottle holder for Professional IC instruments.</p>	
6.2061.110	Tray with sensor for Professional IC Instruments	

6.2061.120

System Connector

Connects an IC module with the footprint of a Professional IC with a Compact IC



6.2630.100

Cover for the deuterium lamp shaft on the UV/VIS Detector SW/MW



6.2630.200


Cover for the VIS lamp shaft on the UV/VIS Detector SW/MW



6.2764.000

Replacement seals to 62839130

Set of seals for Flow cell 10 mm to UV/VIS instruments



6.2804.110

Deuterium lamp (UV) for UV/VIS Detector Vario SW/MW

Replacement deuterium lamp for UV/VIS Detector Vario SW/MW.

