



Electrode shaft

6.1241.060

For 6.1204.XXX electrode tips and 6.2103.1XX contact pins. Electrode plug-in head B (4 mm).

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.





These lists may be subject to change.

Scope of delivery 6.1241.060

Qt.	Order no.	Description
1 PCS	6.1236.020	Sleeve with SGJ 14/12 mm
		Sleeve with SGJ 14/12 mm and O-ring.



Optional accessories

Order no.	Description	
6.1204.130	Silver Electrode Tip Metal electrode tip, silver (Ag). Electrode disk diameter 2 mm. M3 thread. Temperature range: 0 ... 40 °C.	
6.1204.140	Gold Electrode Tip Metal electrode tip, gold (Au). Electrode disk diameter 2 mm. M3 thread. Temperature range: 0 ... 40 °C.	
6.1204.150	Lateral Gold Electrode Tip Metal electrode tip, gold (Au), with lateral electrode surface. Electrode disk diameter 3 mm. M3 thread. Temperature range: 0 ... 40 °C.	
6.1204.170	3 mm platinum electrode tip for CVS Metal electrode tip made of platinum (Pt), diameter of electrode disk 3 mm, polished surface, M3 thread connection. Temperature range: 0 - 40 °C.	

6.1204.180

Ultra Trace electrode tip

Carbon electrode tip from Ultra Trace graphite. Electrode disk diameter 2 mm. M3 thread connection. Temperature range: 0 - 40 °C.



6.1204.190

1 mm platinum electrode tip for CVS

Metal electrode tip made of platinum (Pt), diameter of electrode disk 1 mm ± 0.02 mm, polished surface, shaft made of glass, M3 thread connection. Concentricity error: < 0.2 mm. Temperature range: 0 - 50 °C.



6.1204.600

Glassy carbon electrode tip, shaft made of glass.

Carbon electrode tip made of Glassy-Carbon (GC). Diameter of electrode disk 2 mm ± 0.1 mm, polished surface, shaft made of glass, M3 thread connection, concentricity deviation: < 0.25 mm. Temperature range: 0 - 50°C.



6.1204.610

2 mm platinum electrode tip for CVS

Metal electrode tip made of platinum (Pt), diameter of electrode disk 2 mm ± 0.05 mm, polished surface, shaft made of glass, M3 thread connection. Concentricity error: < 0.3 mm. Temperature range: 0 - 50 °C.



6.2103.110

Contact pin M3, 2 mm

For 6.1241.060 Electrode shaft and 6.1204.1XX Electrode tips. With M3 thread. Used with VA equipment sets and for ELCD applications.



6.2103.120

Contact pin M4 / 2 mm

For 6.1241.060 Electrode shaft and 6.1204.3XX Electrode tips. With M4 thread. Used with VA equipment sets.

