



Flow-through cell for 944

6.2839.130

PEEK flow-through cell for 944 Professional UV/VIS Detector Vario

Below, the accessories are grouped into Scope of delivery and Optional accessories.
Please keep this printout at hand for ordering replacement material.
These lists may be subject to change.

Scope of delivery 6.2839.130

| Qt. | Order no. | Description |
|-------|------------|------------------|
| 2 PCS | 6.2744.060 | Threaded stopper |

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Optional accessories

| Order no. | Description |
|------------|---|
| 6.2764.000 | Replacement seals to 62839130 Set of seals for Flow cell 10 mm to UV/VIS instruments |

