



IC equipment Thin-Layer cell: without electrodes

6.5337.200

Equipment comprised of Thin-Layer cell with additional accessories, without electrodes.

Below, the accessories are grouped into Scope of delivery and Optional accessories.

Please keep this printout at hand for ordering replacement material.

These lists may be subject to change.

Scope of delivery 6.5337.200

Qt.	Order no.	Description
1 PCS	6.1257.820	50 µm spacer to Thin-Layer cell
		50 µm spacer for the amperometric Thin-Layer cell, 3 pcs.



1 PCS

6.1257.840

25 µm spacer to Thin-Layer cell

25 µm spacer for the amperometric Thin-Layer cell, 3 pcs.



1 PCS

6.1831.010

PEEK capillary 0.25 mm i.d. / 3 m

For all IC components.



1 PCS

6.2621.140

Hexagon key 2.5 mm



1 PCS

6.2744.014

Pressure screw 2x

With UNF 10/32 connection. For the connection of PEEK capillaries



1 PCS

6.2802.000

Polishing set for solid-state electrodes

Polishing set with 1 polishing cloth and about 2 g aluminum oxide powder (grain size 0.3 µm)

