



NIRS XDS Process Analyzer – MicroBundle 4 Channels

A629280120C

The NIRS XDS Process Analyzer – MicroBundle provides the next generation of process analyzers for real-time analysis in the pharmaceutical and chemical industries. Non-destructive, accurate measurements of practically any sample type (powders, slurries, liquids,..) are performed directly in the process line, granulator, dryer or reaction vessel. Up to 4 probes and/or flow-cells can be connected to the analyzer. All 4 channels can be configured independently from each other and the micro bundle fiber optics allows the 4 measuring points to be up to 35 meter away from the XDS NIR process analyzer.

Below, the accessories are grouped into Scope of delivery and Optional accessories.
Please keep this printout at hand for ordering replacement material.
These lists may be subject to change.

Optional accessories

Order no.	Description
-----------	-------------

A649281190 NIRS XDS Process Contact Lamp 50W, 12 Volt- White lead

Replacement lamp with contact for NIRS Process instruments. 50W, 12 Volt- White lead.

