




IC Conductivity Detector

2.850.9010

Detector de conductividad de alto rendimiento, inteligente y compacto para los aparatos CI inteligentes. La extraordinaria constancia de temperatura, el tratamiento completo de la señal dentro del bloque detector protegido y DSP (tratamiento digital de la señal controlado por microprocesador) de última generación garantizan la máxima precisión de la medida. Gracias a la zona de trabajo dinámica no es necesario el cambio de la zona (ni siquiera automático).

Partes/accesorios 2.850.9010

Qt.	Order no.	Descripción
1 PCS	1.850.9010	IC Conductivity Detector

Compact and intelligent high performance conductivity detector for intelligent IC instruments. Outstanding temperature stability, the complete signal processing within the protected detector block and the latest generation of DSP – Digital Signal Processing – guarantee the highest precision of the measurement. No change of measuring ranges (not even automatic ones) is required, due to the dynamic working range.



1 PCS

6.2744.014

Pressure screw 2x

With UNF 10/32 connection. For the connection of PEEK capillaries

