



Metrosep A Supp 17 - 250/4,0

6.01032.430

La Metrosep A Supp 17 - 250/4,0 combina una alta eficacia de separación con una buena relación calidad-precio, sin que resulte necesario utilizar un horno para columnas. El material base de poliestireno/divinilbenceno utilizado garantiza la larga vida útil de la columna. En esta columna se pueden resolver las tareas de separación complejas.

Partes/accesorios 6.01032.430

Qt.	Order no.	Descripción
2 PCS	6.2744.060	Threaded stopper

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Accesorios opcionales

Order no.	Descripción	
6.01032.500	Metrosep A Supp 17 Guard/4.0	
	The Metrosep A Supp 17 Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. Thanks to the "On Column Guard System", the guard column is very easy to handle. The guard column screws easily onto the analytical column. No tools are required.	
6.01032.510	Metrosep A Supp 17 S-Guard/4.0	
	The Metrosep A Supp 17 S-Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	
6.01032.530	Metrosep A Supp 17 S-Guard - 50/4.0	
	The Metrosep A Supp 17 S-Guard 50/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	