



Metrosep C Supp 2 - 250/4,0

6.01053.430

La columna más larga de la familia Metrosep C Supp 2 es la Metrosep C Supp 2 - 250/4,0. El material de separación de la Metrosep C Supp 2 está basado en un copolímero de divinilbenceno-poliestireno con grupos carboxilo. Gracias a la separación optimizada de sodio y amonio que ofrece este material de separación, esta columna es perfectamente adecuada para la determinación de concentraciones muy bajas de amonio, además de una gran cantidad de sodio. La columna se usa con supresión secuencial. Por lo tanto, es especialmente adecuada para la determinación de concentraciones en la gama media de $\mu\text{g/L}$ e inferiores.

Partes/accesorios 6.01053.430

Qt.	Order no.	Descripción
2 PCS	6.2744.060	Threaded stopper

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Accesorios opcionales

Order no.	Descripción
6.01053.500	<p>Metrosep C Supp 2 Guard/4.0</p> <p>The Metrosep C Supp 2 Guard/4.0 contains the C Supp 2 column material and is used to protect Metrosep C Supp 2 cation columns. Particles and contamination are reliably retained, considerably prolonging the service life of the analytical separation column. The Metrosep C Supp 2 Guard/4.0 also works based on the "On Column Guard System" and is screwed directly onto the separation column with virtually no dead volume.</p>

