



Metrosep A Supp 10 - 150/2,0

6.1020.220

La columna de separación Metrosep A Supp 10 - 150/2,0 está basada en un copolímero de poliestireno-divinilbenceno de alta capacidad, con un tamaño de partículas de solo 4,6 µm. Este concepto de columnas de probada eficacia y optimizado por Metrohm se caracteriza por su construcción robusta, su gran selectividad y sus excelentes resultados de separación. Las columnas de separación de 2 mm Metrosep A Supp 10 están hechas del mismo material que las columnas de separación de 4 mm correspondientes. Las propiedades de la columna se pueden adaptar a la aplicación actual mediante la temperatura, el flujo y la composición del eluyente.

La columna de separación Metrosep A Supp 10 - 150/2,0 es apta para las tareas de separación complejas con elevadas diferencias de concentración. La versión microbore consume poco eluyente y, por ello, es especialmente apta para aplicaciones IC-MS.

Partes/accesorios 6.1020.220

Qt.	Order no.	Descripción
-----	-----------	-------------

2 PCS

6.2744.060

Threaded stopper

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Accesorios opcionales

Order no.	Descripción
6.1020.600	<p>Metrosep A Supp 10 Guard/2.0</p> <p>The Metrosep A Supp 10 Guard/2.0 column reliably protects the A Supp 10 analytical microbore separation columns against contamination. Thanks to the "On Column Guard System", the guard column is very easy to handle. The guard column screws easily and directly onto the analytical column without tools</p>

