



942 Extension Module Vario SeS/PP

2.942.0500

Le 942 Extension Module Vario SeS/PP est un module d'extension pour la famille d'appareils Professional IC Vario. Il permet d'intégrer une suppression séquentielle complète avec une pompe péristaltique pour la régénération du supprimeur dans un système Professional IC Vario.

Applications typiques :

- Suppression séquentielle pour un canal d'analyse supplémentaire

Contenu de la livraison 2.942.0500

Qt.	Order no.	Description
-----	-----------	-------------

The 942 Extension Module Vario SeS/PP is an extension module for the Professional IC Vario line of instruments. It permits the integration of a complete sequential suppression with a peristaltic pump for suppressor regeneration in a Professional IC Vario system.

Typical applications:

- Sequential suppression for an additional analysis channel



For the connection of 1/16 in. capillaries. Used in conjunction with MSM auxiliary solutions and in Metrohm Inline Sample Preparation.



Bottle for auxiliary solutions.



Capillary for inline dialysis, for Dialysis Unit, IC Dialysis Sample Processor, IC Liquid Handling Dialysis Unit




2 PCS

6.1826.420

PharMed® pump tubing (orange/yellow), 3-stopper

For MSM regeneration with peristaltic pump.



1 PCS

6.1831.070

PEEK capillary 0.75 mm i.d., 70 cm

For Advanced VA Sample Processor



1 PCS

6.2156.070

Cable Extension Module - Professional IC, 1 m

Cable connecting the extension module with the Professional IC instrument



1 PCS

6.2251.000

Colored sleeves for capillaries

Colored pieces of heat shrink tubing for capillary coding. Three pieces each of five different colors.



1 PCS

6.2744.034

Coupling olive/UNF 10/32, 2x

Connection between pressure screw and pump tubing. 2 pieces. For IC instruments with peristaltic pump.



2 PCS

6.2744.180

Pump tubing connector with security lock and filter

For the connection of a pump tubing and a capillary with built-in filter



1 PCS





6.5000.020

Accessory kit: Vario/Flex SeS

Set of accessories for sequential suppression (SeS) for Professional IC Vario and Compact IC Flex instruments. Without Suppressor Rotor.



Accessoires optionnels

Order no.	Description	
6.2103.170	Adapter to Leak Sensor at Professional IC Adapter to connect two leak sensors to a Professional IC instrument	
6.2832.000	MSM Rotor A Suppressor rotor for all IC instruments with MSM (Metrohm Suppressor Module)	
6.2842.000	MSM-HC Rotor A Suppressor rotor for all IC instruments with MSM-HC (Metrohm Suppressor Module with high capacity)	
6.2842.020	Adapter sleeve, MSM Not only the MSM Rotor A but also the MSM-LC Rotor A can be installed in the rotor housing with the aid of the adapter sleeve.	

6.2842.200

MSM-HC Rotor C

Suppressor rotor for all IC instruments with MSM-HC drive (Metrohm Suppressor Module with high capacity) for cation suppression.



6.2844.000

MSM-LC Rotor A

Suppressor rotor for use with 2 mm columns.



Client/server-compatible chromatography software from Metrohm for controlling all intelligent Professional IC systems, Compact IC systems and their peripherals, all detectors and the various Autosamplers, 800 Dosino, 771 Compact Interface, etc.

The software permits checks, data acquisition, data evaluation and data monitoring as well as report generation of ion chromatographic analyses. Data and method are centrally stored on a Server.



Graphical user interface for routine operations, extensive database programs, method development, configuration and manual control panel; very flexible user management, efficient database operations, extensive data export functions, individually configurable report generator, control and monitoring of all system components and the chromatography results.

MagIC Net Multi complies fully with FDA Regulation 21 CFR Part 11 as well as with GLP.

MagIC Net is available in 15 dialog languages: German, English, Chinese, Traditional Chinese, French, Italian, Spanish, Portuguese, Bulgarian, Czech, Hungarian, Japanese, Korean, Russian, Slovakian

With this version, the graphic user interface has been modernized, which improves, among other things, the scaling and sharpness of the user interface on 4K monitors.

Performance for client/server systems with servers outside the in-house company network has been improved.

Client/server version with 3 licenses
