



Metrosep A Supp 17 - 250/4,0

6.01032.430

La Metrosep A Supp 17 - 250/4,0 combine des performances de séparation élevées et un rapport performances/prix avantageux, sans nécessiter de four à colonne. Le polystyrène-divinylbenzène employé comme matériau de base garantit une longue durée de vie à la colonne. Cette colonne permet de réaliser des tâches de séparation complexes.

Contenu de la livraison 6.01032.430

Qt.	Order no.	Description
2 PCS	6.2744.060	Threaded stopper

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Accessoires optionnels

Order no.	Description	
6.01032.500	Metrosep A Supp 17 Guard/4.0	
	The Metrosep A Supp 17 Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. Thanks to the "On Column Guard System", the guard column is very easy to handle. The guard column screws easily onto the analytical column. No tools are required.	
6.01032.510	Metrosep A Supp 17 S-Guard/4.0	
	The Metrosep A Supp 17 S-Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	
6.01032.530	Metrosep A Supp 17 S-Guard - 50/4.0	
	The Metrosep A Supp 17 S-Guard 50/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	