



Metrosep A Supp 17 - 250/4,0

6.01032.430

La Metrosep A Supp 17 - 250/4,0 combina un'elevata efficienza di separazione con un buon rapporto prezzo/prestazioni e questo senza rendere necessario un forno per colonna. Il materiale di base polistirene/divinilbenzene utilizzato garantisce una lunga durata della colonna. Con questa colonna è possibile risolvere compiti di separazione complessi.

Parti incluse 6.01032.430

Qt.	Order no.	Descrizione
2 PCS	6.2744.060	Threaded stopper

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



Accessori opzionali

Order no.	Descrizione	
6.01032.500	Metrosep A Supp 17 Guard/4.0	
	The Metrosep A Supp 17 Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. Thanks to the "On Column Guard System", the guard column is very easy to handle. The guard column screws easily onto the analytical column. No tools are required.	
6.01032.510	Metrosep A Supp 17 S-Guard/4.0	
	The Metrosep A Supp 17 S-Guard/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	
6.01032.530	Metrosep A Supp 17 S-Guard - 50/4.0	
	The Metrosep A Supp 17 S-Guard 50/4.0 reliably protects the Metrosep A Supp 17 analytical separation columns against contamination. The guard column is simply connected to the separation column using capillary connections. No tools are required.	