



Cavo remoto, IC - Agilent ICP-MS

6.2141.410

Cavo di collegamento per la sincronizzazione di sistemi IC Metrohm (930 IC Flex e 940 Professional IC) e sistemi Agilent ICP-MS

Accessori opzionali

Order no.	Descrizione
6.2141.420	Connecting cable, Remote Box MSB
	Connecting cable between connection box and Remote Box MSB



6.2141.430 Connecting cable, leak sensor

Connecting cable between connection box and leak sensor inlet of the IC



6.2149.310 Connection Box, remote control, ICP-MS

Connector for use as interface between Metrohm IC (Remote Box MSB) and Agilent ICP-MS in MassHunter 5.3 and higher.

