



Equipaggiamento IC: eluente supplementare sull'Eluent Production Module

6.5330.090

Set di accessori per l'Eluent Production Module. Comprende tutti i pezzi per l'aggiunta di un eluente. I sensori di livello devono essere ordinati conformemente all'applicazione.

Parti incluse 6.5330.090

Qt.	Order no.	Descrizione
1 PCS	6.1580.250	807 Dosing Unit 50 mL without accessories

807 Dosing Unit with integrated data chip with 50 mL glass cylinder and light protection, mountable to a reagent bottle with ISO/DIN GL 45 glass thread.



1 PCS

6.1602.160

Bottle attachment GL 45 for eluents and reagents

For eluent, reagent, and rinsing bottles, with connectors for the adsorber tube and the aspiration tubing.



1 PCS

6.1608.070

Eluent bottle / 2 L / GL 45




1 PCS

6.1618.020

Thread adapter S 40 to GL 45

Adapter for bottles with S40 thread (Merck...) to GL45.



1 PCS

6.1618.050

Thread adapter 40 mm to GL 45

Adapter for bottles with 40 mm thread to GL45.



1 PCS

6.1619.000

Adsorber tube for 807 Dosing Unit



1 PCS

6.1621.000

Container 10 L

As rinsing or waste container in automated systems.



1 PCS

6.1621.100

Cap for 10-L container

Cap for 10-L container. For easy and safe transportation of filled containers.



1 PCS

6.1624.000

Adapter SGJ 14 for 6.1619.XXX Adsorber tube

Adapter SGJ 14. Part of 6.1619.010 for Dilution Sample Processor.



1 PCS

6.1626.000

Bottle attachment GL 45 for level sensor

This bottle attachment, fitted with the 6.2769.XXX sensors, results in the level sensors EMPTY and FULL, respectively, for bottles and canisters.



4 PCS

6.1805.530

FEP tubing / M6 / 2 m

With light and kink protection



1 PCS

6.1808.280

Adapter 807 Dosing Unit Port 4, M6 inner

Adapter for using Port 4 of the 807 dosing Unit for connection with an FEP tubing / M6.



1 PCS

6.1815.010

Spiral band 0.5 m

For holding together different cables or tubing.



1 PCS

6.1819.100

FEP aspiration tubing to 2 L bottle

Aspiration tubing to bottle attachment with M6 connector. For the production of eluents.



1 PCS

6.1819.110

FEP aspiration tubing to canister

Aspiration tubing to canister attachment with M6 connector. For the production of eluents.




1 PCS

6.2057.210

Holder for Dosino to IC instruments

Mounting part for Dosinos at the IC instrument housing.



1 PCS

6.2151.060

Cable for Level Control and Eluent Production Module

Connecting cable for sensor and Level Control or Eluent Production Module.



1 PCS

6.2744.200

Adapter UNF 10/32 outer / M6 inner

Connecting 1/16 in. PEEK capillaries and transfer tubing (M6)



Accessori opzionali

Order no.	Descrizione	
6.2769.000	FULL sensor for level sensor	
6.2769.100	EMPTY sensor for level sensor for 1 L bottles	
6.2769.110	EMPTY sensor for level sensor for 2 L bottles	
6.2769.120	EMPTY sensor for level sensor for 10 L canisters	