



# Metrosep C 6 - 150/4.0

6.1051.420

C 6 Metrosep C 6 - 150/4.0

**6.1051.420**

Qt.	Order no.	
2 PCS	<b>6.2744.060</b>	<b>Threaded stopper</b>

For UNF 10/32. Stopper for IC, e.g. for the sealing of columns.



**Order no.****6.1051.500****Metrosep C 6 Guard/4.0**

The Metrosep C 6 Guard/4.0 contains the C 6 column material and is used to protect against particles and contamination. This considerably lengthens the service life of the analytical separation column. The Metrosep C 6 Guard/4.0 works according to the "On Column Guard System" and is screwed directly onto the respective separation column with virtually no dead volume.

**6.1051.510****Metrosep C 6 S-Guard/4.0**

The Metrosep C 6 S-Guard/4.0 contains the C 6 column material and is used to protect it against particles and contamination. This considerably lengthens the service life of the analytical separation column.

