



Basic set of accessories for a Professional IC Vario or Compact IC Flex.



1 PCS

**6.1602.210**

**Attachment 5 x UNF 10/32 for «Waste Collector»**

Attachment for holding up to 5 waste capillaries.



---

1 PCS

**6.1807.010**

**Y-connector for tubing 6-9 mm i.d.**

Connector for waste tubing



---

1 PCS

**6.1815.010**

**Spiral band 0.5 m**

For holding together different cables or tubing.



---

2 PCS

**6.1816.020**

**Silicone tubing 6 mm i.d., 1 m**

For waste tubing.



1 PCS

**6.2057.220**

**Holder to Waste Collector**

Holder for fastening the Waste Collector to the IC instrument.



---

1 PCS

**6.2151.020**

**Cable USB A - USB B 1.8 m**

USB connecting cable



---

1 PCS

**6.2251.000**

**Colored sleeves for capillaries**

Colored pieces of heat shrink tubing for capillary coding. Three pieces each of five different colors.



---

1 PCS

**6.2617.010**

**Tool for piston seal**

For removing and assembling the piston seal for all standard pump heads



2 PCS

**6.2621.000**

**Adjustable wrench**

Max. opening: 20 mm. For IC instruments



---

1 PCS

**6.2621.030**

**Hexagon key 4 mm**



---

1 PCS

**6.2621.050**

**1/4 in. wrench**

For 1/4 in. screws. For IC instruments



---

1 PCS

**6.2621.080**

**Capillary cutter**

Cutting tool for simple cutting of plastic capillaries, 1/16" and 1/8", including 5 replacement blades.



1 PCS

6.2621.100

3 mm hex key for IC Sample Processors



---

2 PCS

6.2739.000

Wrench

For tightening connectors



---

1 PCS

6.2743.080

Stopper for overflow (ProfilC), 5 pieces

For Professional IC instruments



---

1 PCS

6.2765.000

Container with GL 45 drainage to the "Waste Collector"

Container with drainage to the "Waste Collector".

