



# IC equipment Thin-Layer cell: without electrodes

6.5337.200

Equipment comprised of Thin-Layer cell with additional accessories, without electrodes.

Phạm vi giao hàng 6.5337.200

| Qt.   | Order no.  | Description                                               |
|-------|------------|-----------------------------------------------------------|
| 1 PCS | 6.1257.820 | 50 µm spacer to Thin-Layer cell                           |
|       |            | 50 µm spacer for the amperometric Thin-Layer cell, 3 pcs. |



1 PCS

6.1257.840

25 µm spacer to Thin-Layer cell

25 µm spacer for the amperometric Thin-Layer cell, 3 pcs.



---

1 PCS

6.1831.010

PEEK capillary 0.25 mm i.d. / 3 m

For all IC components.



---

1 PCS

6.2621.140

Hexagon key 2.5 mm



---

1 PCS

6.2744.014

Pressure screw 2x

With UNF 10/32 connection. For the connection of PEEK capillaries



1 PCS

6.2802.000

Polishing set for solid-state electrodes

Polishing set with 1 polishing cloth and about 2 g aluminum oxide powder (grain size 0.3 µm)

